


ORIGINAL

DRAWING #	100303	Rev.
3/19/10	Removed L/L Cryo Outlet	A

TOP VIEW




IF THE PUMPS ARE LOCATED IN A SERVICE CHASE, ELECTRICAL DISCONNECTS MUST BE PROVIDED IN THE CHASE.

10' CRYO LINES ARE STANDARD, OTHER LENGTHS AVAILABLE AS AN OPTION.

CRYO COMPRESSOR(S)

REAR VIEW



NOTICE: NOT FOR USE OR DISCLOSURE OUTSIDE OF MAT-VAC TECHNOLOGY INC. EXCEPT UNDER WRITTEN AGREEMENT

TOLERANCE	TITLE	8X Series Sputter System
Angles $\pm 1/2^\circ$	Material Used	Modernized MRC 8600 Series
.XX $\pm .01$	Init. Date	
.XXX $\pm .005$	Drawn by: MNS	03/07/10
Fractions $\pm 1/64$	Checked by:	
Finish Machined	Approved by:	
	Designed by:	
	QC Approved:	
Part of Assembly #	UNLESS OTHERWISE SPECIFIED ALL UNITS ARE IN INCHES.	
	SCALE: _____ DO NOT SCALE DRAWING	
	1 OF 3	DRAWING #100303

MAT-VAC TECHNOLOGY, INC.
 415 Orange Ave.
 Daytona Beach, FL 32114
 (386) 238-7017 FAX (386) 238-0976
 www.mat-vac.com

ORIGINAL

DRAWING #	100303	Rev.

1. AIR - COMPRESSED:
 Pressure: Ambient *
 Quality: Dry, oil free and Particulate Free. **
 FLOW RATE: 400 SCFM
- * MEASURED AT THE CONNECTION ON THE UTILITY PANEL AND HELD CONSTANT WITHIN 5 PSI
 ** SUCH AIR SHOULD HAVE THE FOLLOWING PROPERTIES:
 DEW POINT: -40° F. (4° C.) OR LOWER.
 OIL CONTENT: LESS THAN ONE PART PER MILLION
 PARTICLE SIZE: LESS THAN .09 MICRON.
 EQUIPMENT TO SUPPLY SUCH AIR IS AVAILABLE FROM PALL CORP., PORT WASHINGTON, N.Y.
 AND OTHERS SUPPLIERS.
2. DRY NITROGEN:
 PRESSURE: 15-20 PSIG. *
 QUALITY: HIGH PURITY, DRY
 FLOW RATE: 120 SCFM
- * MEASURED AT THE CONNECTION ON THE UTILITY PANEL AND HELD CONSTANT WITHIN 5 PSIG.
3. WATER:
 PRESSURE: 40-50 PSIG (SYSTEM DIFFERENTIAL PRESSURE TO BE 40 PSIG OR HIGHER)
 TEMPERATURE: 50° F (10°C) - 74° (24° C.) AND SUFFICIENTLY ABOVE AMBIENT DEW POINT TO
 PREVENT CONDENSATION.
- QUALITY: PARTICLES LESS THAN 100 MICRON
 RESISTIVITY: 100 KOHMS/CM OR GREATER *
 FLOW RATE: 5.0 GAL /MIN.
- * MEASURED INTO AN OPEN CONTAINER.
4. ARGON:
 PRESSURE: 5-10 PSIG.
 QUALITY: PURITY 99.999% SCIENTIFIC GRADE ULTRA HIGH PURITY *
- * RECOMMEND STAINLESS STEEL INTERCONNECT PLUMBING AND ULTRA HIGH PURITY STAINLESS STEEL DUAL STAGE
 REGULATOR, COMPATIBLE FOR LEAK TESTING, TO BE USED FOR ARGON.
 ALL GAS LINES MUST BE LEAK TIGHT TO SYSTEM TO INSURE PURITY.
5. AIR - ROOM:
 IT IS RECOMMENDED THAT THE ROOM AMBIENT AIR BE 70° F (22°C) +/- 5° (2.3° C).
 CLEAN ROOM ENVIRONMENT, CLASS 10,000 OR BETTER IS RECOMMENDED. RELATIVE HUMIDITY 40% - 60%
 (NON-CONDENSING).

6. AUXILIARY POWER FOR TEST AND MAINTENANCE:
 -100 VAC 60 HZ., 4 OUTLETS MINIMUM, 15 AMP. EA., AVAILABLE IN IMMEDIATE AREA.
 -A TELEPHONE SHOULD BE LOCATED NEAR THE SYSTEM FOR THE CONVENIENCE OF SERVICE PERSONNEL.
 -A HIGH SPEED INTERNET CONNECTION SHOULD BE LOCATED NEAR THE SYSTEM FOR THE CONVENIENCE OF THE
 SERVICE PERSONNEL.
- 7A ELECTRICAL POWER:
 208 VAC 60 HZ. - Y CONFIGURATION, 3 PHASE, 5 WIRE, SEPARATE GROUND AND NEUTRAL
 NOTE: CUSTOMER CAN UTILIZE AN EXTERNAL 45 KVA STEP-DOWN OR STEP-UP
 TRANSFORMER TO ACCOMMODATE OTHER AC POWER INPUT VOLTAGES.
 50 HZ. COMPATABILITY IS AVAILABLE UPON REQUEST.
 (REQUIRES FREQUENCY CONVERTER FOR CRYO-PUMP COMPRESSOR AND 50 HZ. MOTOR
 ON MECHANICAL PUMP AND HYDRAULIC PUMP.)
- OVERALL LINE IMPEDANCE: 0.1 OHM MAX.
 MAIN POWER LINE MUST BE TRANSIENT FREE.
 PRIMARY AC POWER INPUT IS TO THE REAR OF THE ELECTRONICS CONTROL RACK
 THE ELECTRONICS CONTROL RACK PROVIDES ALL AC & DC POWER
 TO THE MAIN VACUUM SYSTEM.
- 7B THE MECHANICAL PUMP, THE CRYO PUMP(S), AND THE DC AND RF SPUTTERING POWER SUPPLIES
 GET THEIR AC POWER FROM A SEPARATE PANEL LOCATED AT THE REAR OF THE
ELECTRONICS CONTROL RACK
8. ALL UTILITY CONNECTIONS SHOULD BE FLEXIBLE TO ALLOW SOME REPOSITIONING OF THE SYSTEM WHEN
 NECESSARY FOR MAINTENANCE PERSONNEL ACCESS. COMPLETE ACCESS, A MINIMUM OF 24 INCHES,
 ALL AROUND THE SYSTEM IS REQUIRED FOR SERVICING.
9. SHOULD IT BECOME NECESSARY AT ANY TIME TO CHECK THE SYSTEM FOR LEAKS, IT IS THE CUSTOMERS
 RESPONSIBILITY TO PROVIDE A WORKING LEAK DETECTOR AT A MINIMUM SENSITIVITY OF 2.0 X 10⁻¹⁸ ST. ATM.
 CC/SEC. FOR HELIUM AT FULL PUMPING SPEED TO BE USED BY MAT-VAC SERVICE PERSONNEL.
10. EXTERNAL SHUTDOWN VALVES AND FUSE DISCONNECTS ARE RECOMMENDED FOR ALL UTILITIES. DUAL STAGE
 ULTRA HIGH PURITY REGULATORS ARE REQUIRED FOR ALL PROCESS GASSES.
11. SYSTEM MAIN FRAME MUST BE GROUNDED TO THE NEAREST HIGH VOLTAGE EQUIPMENT EARTH GROUND.
 CLOSE PROXIMITY TO THE SYSTEM IS PREFERABLE.
 ALL EQUIPMENT GROUNDING MUST BE APPROVED BY A LICENSED ELECTRICIAN AS PER NFPA 70: NATIONAL
 ELECTRIC CODE, OR OTHER COUNTRY EQUIVALENT.
 THE SYSTEM ELECTRONICS CONTROL RACK IS TO BE GROUNDED TO THE SYSTEM MAIN FRAME.
12. CAUTION: EQUIPMENT FAILURES ATTRIBUTED TO:
 - INSUFFICIENT COOLANT FLOW
 - INPUT POWER OF INSUFFICIENT QUALITY
 - FAILURE TO MAINTAIN THE INTEGRITY OF COOLING WATER CIRCUIT.
 CAUTION MUST BE EXERCISED WHEN A CLOSED LOOP WATER RECIRCULATOR (CHILLER) IS UTILIZED TO PREVENT
 EXCESSIVE WATER/BACK PRESSURE WHICH MAY DEGRADE WATER FITTING SEALS RESULTING IN MAJOR WATER LEAKS.
13. INITIAL INSPECTION OF ALL UTILITIES AND INITIAL TURN-ON OF THE SYSTEM BY A MAT-VAC FIELD
 REPRESENTATIVE IS RECOMMENDED.





NOTE; ANY OTHER DEVIATION FROM THE REQUIREMENTS OF THIS DOCUMENT
 MAY EFFECT THE WARRANTY STATUS OF THE EQUIPMENT.

NOTICE: NOT FOR USE OR DISCLOSURE OUTSIDE OF MAT-VAC TECHNOLOGY INC. EXCEPT UNDER WRITTEN AGREEMENT		
TOLERANCE	TITLE	8X Series Sputter System
Angles ±1/2°	Material Used	Modernized MRC 8600 Series
.XX ±.01	Init. Date	
.XXX ±.005	Drawn by: MNS	03/07/10
Fractions ±1/64	Checked by:	
Finish Machined	Approved by:	
	Designed by:	
	QC Approved:	
Part of Assembly #	UNLESS OTHERWISE SPECIFIED ALL UNITS ARE IN INCHES.	
	SCALE: _____	
	DO NOT SCALE DRAWING	
	2 OF 3	
		DRAWING #100303

MAT-VAC
 TECHNOLOGY, INC.
 415 Orange Ave.
 Daytona Beach, FL 32114
 (386) 238-7017 FAX (386) 238-0976
 www.mat-vac.com

ORIGINAL

DRAWING #	100303	Rev.
3/19/10	Removed L/L Cryo Outlet	A



PANEL
DETAILS

NOTICE: NOT FOR USE OR DISCLOSURE OUTSIDE OF MAT-VAC TECHNOLOGY INC. EXCEPT UNDER WRITTEN AGREEMENT

TOLERANCE	TITLE	8X SERIES SPUTTER SYSTEM
Angles ±1/2°	Material Used	Modernized MRC 8600 Series
.XX ±.01	Init. Date	 MAT-VAC TECHNOLOGY, INC. 415 Orange Ave. Daytona Beach, FL 32114 (386) 238-7017 FAX (386) 238-0976 www.mat-vac.com
.XXX ±.005	Drawn by: MNS 03/07/10	
Fractions ±1/64	Checked by:	
Finish Machined	Approved by:	
	Designed by:	
Part of Assembly #	QC Approved:	
UNLESS OTHERWISE SPECIFIED ALL UNITS ARE IN INCHES.	SCALE: _____	3 OF 3
		DRAWING #100303